




**Feature**

- Video/Audio Wireless Transmitter Module
- 500/1000 mW output power instant switchable
- Compact size module
- Highly integrated circuit
- 8 channels DIP switch selectable
- Digital Phase-Lock-Loop circuit without temperature drifting problem
- Light aluminum case total weight only 17 gram


**Specification**

Model	TX-120015	TX-240015
Frequency Band	1200MHz	2400MHz
Available Channel	8 Ch	8 Ch
Audio Subcarrier	5.5MHz	6.5MHz
Operating Voltage	DC 12V	
Operating Current	300~350mA	
Trans. Range	0.5W : 120m / 1W : 200m (Open space)	
Transmission Power	0.5W : 27±0.5 dBm / 1W : 30±1 dBm	
Power Consumption	3.6W	
Operating Temperature	0~60°	
Operating Humidity	20~80%	
Channel Selection	Dip Switch	
Antenna Connector	SMA Connector	
Frequency Lock Method	Digital Phase Lock Loop	
Weight	17±1g	
Dimension	37.5 x 27 x 12.6 mm (L x W x H)	

**500mW**




**1000mW**



**Wire Specification**



GND : Black  
Audio : White  
DC : Red  
Video : Yellow



Model	TX-120015	TX-240015
CH1	1080	2410
CH2	1120	2430
CH3	1160	2450
CH4	1200	2470
CH5	1010	2370
CH6	1040	2390
CH7	1240	2490
CH8	1280	2510