




## Feature

- Video/Audio Wireless Transmitter Module
- RF output power 1000mW / +30dBm
- Highly integrated circuit
- Digital Phase-Lock-Loop circuit
- 8 channels DIP switch selectable
- Copper-Nickel-Zinc Alloy case
- Ceramic heat spreaders


## Specification

Model	TX-121000	TX-241000
Frequency Band	1200MHz	2400MHz
Available Channel	8 Ch	8 Ch
Audio Subcarrier	5.5MHz	6.5MHz
Operating Voltage	DC 12V	
Operating Current	≤350mA	
Trans. Range	200m (Open space)	
Transmission Power	30±1 dBm	
Power Consumption	≤4.2W	
Operating Temperature	0~60°	
Operating Humidity	20~90%	
Channel Selection	Dip Switch	
Antenna Connector	SMA Connector	
Frequency Lock Method	Digital Phase Lock Loop	
Weight	27±1g	
Dimension	59.8 x 25 x 11.3 mm (L x W x H)	


### 500mW



## Wire Specification



GND : Black  
 Audio : White  
 DC : Red  
 Video : Yellow



Model	TX-121000	TX-241000
CH1	1080	2410
CH2	1120	2430
CH3	1160	2450
CH4	1200	2470
CH5	1010	2370
CH6	1040	2390
CH7	1240	2490
CH8	1280	2510