


1M08750AR-M01



Unit: mm

Specification

Model	1M08750AR-M01
EFL	0.878
FBFL	1±0.2mm
F/NO	5±5%
Sensor type	1/11"
Lens composition	3P+1
Image circle	Ø1.81 mm
Total Track	2.744
TV distortion	< -47.5%
Relative Illumination	> 68%
FOV	V: 56.2° ; H: 95.1° ; D: 120°
Chief ray angle	< 30°
Barrel Dimension	Ø2.90