



Feature

- High performance
- Outstanding quality.
- 5 Megapixel resolution.
- Miniature size



Specification

Model	xxx-R363xx -62
Pixel size	1.12 x 1.12 μm
Active image size	2.9 x 2.18mm
Resolution	2592 x 1944 @30fps MJPG/YUV
Image sensor	1/5" CMOS color
Sensor scan mode	progressive
Video format	MJPG / YUV
Sensitivity	3.6V/lux-sec
Max SNR	37 dB
Max dynamic range	64.7 dB
Storage temperature	-30 to 60 Degree C
Working temperature	-10 to 45 Degree C
Built-in lens	3.0mm/F2.4 (H=51°36';V=39°56';D=62°21')
Power source	DC 5V
Power current	220mA
OS support	windows 7 (USB 2.0), windows 10, android
Microphone	external
Interface	USB 2.0

Mini Spy Camera
Shirt Button Pinhole Hidden Camera



Lens Cover KIT for User Change Easily!



TYT - R36331 - 62

Connector	Camera type	Cover type	Lens angle
TYT USB 3.0 type C TYD USB 3.0 type A XT USB 2.0 type C XD USB 2.0 type C XM USB 2.0 Micro USB B type	R363 color (with case)	20 screw 21 button (sliver) 22 screw 23 screw 24 screw 25 button (black) 31 button (black)	62 3.0mm/F2.4 (62°)