


Specification

Product Image						
Dimensions (mm)						
Model	UCD-210	UCD-210M	UCD-211	UCD-211M	UCD-212	UCD-213
Dimensions (mm)	86(L) x 23(W) x 12(H)	86(L) x 20.3(W) x 10(H)	99(L) x 29(W) x 15(H)	99(L) x 25(W) x 10(H)	99(L) x 29(W) x 15(H)	88.9(L) x 63(W) x 10(H)
Video Input	CVBS (NTSC / PAL)	CVBS (NTSC / PAL)	CVBS (NTSC / PAL)	CVBS (NTSC / PAL)	CVBS (NTSC / PAL)	CVBS (NTSC / PAL)
UVC Output	UCD-210 640 x 480 UCD-210HN 720 x 480 UCD-210HP 720 x 576	UCD-210M 640 x 480 UCD-210MHN 720 x 480 UCD-210MHP 720 x 576	UCD-211 640 x 480 320 x 240 @ 30fps UCD-211-N 720 x 480 / 640 x 480 320 x 240 @ 30 fps UCD-211-P 720 x 576 / 640 x 480 320 x 240 @ 30fps	UCD-211M 640 x 480 320 x 240 @ 30fps UCD-211M-N 720 x 480 / 640 x 480 320 x 240 @ 30 fps UCD-211M-P 720 x 576 / 640 x 480 320 x 240 @ 30fps	UCD-211M 640 x 480 320 x 240 @ 30fps UCD-212-5.0-N 720 x 480 / 640 x 480 320 x 240 @ 30 fps UCD-212-5.0-P 720 x 576 / 640 x 480 320 x 240 @ 30fps	UCD-213 640 x 480 @ 60fps UCD-213HD 1280 x 720 @ 60 fps
UVC Format Output	MJPEG	MJPEG	MJPEG, YUV, H.264	MJPEG, YUV, H.264	MJPEG, YUV, H.264	YUV
Audio	Support	Support	Support (48kHz)	Support (48kHz)	Support (48kHz)	Support (48kHz)
OS Support	Windows XP 、 Vista 、 Windows 7 、 Windows 8 、 Windows 10 、 MAC OS					Windows 8.1 、 Windows 10
Interface	4 Pin IRIS for Camera / USB 2.0 A type for output					
Power Input	DC 5V					
Power Output	DC 5V					
Storage Temperature	-40°C~85°C					
Working Temperature	-10°C~60°C					

Driver Free	No use to install driver to USB Video Class
Compact Size	Perfect for travel and portable use.
Plug & play	for USB video class
Upscale Image Quality (Model: UCD-213 series)	QVGA image pixel upscale to 1280 x 720(720p)
Live Video Calls	SKYPE ,YouTube and JoinNetso on
Power Output	2 power output for select (DC 5V / DC3.3V)



UCD-211M-5.0-N

SERIES	FORMAT / OS SUPPORT	CASE	POWER OUTPUT	UVC OUTPUT
UCD	CVBS to UVC Grabber Card			
	Format Output			
	210 MJPG	M Board Type	210	210
	211 MJPG, YUV, H.264	N/A Case Type	N/A DC 5V	N/A 640 x 480
	212 MJPG, YUV, H.264		3.3V DC 3.3V	211 / 212
	213 YUV		211 / 212 / 213	N/A 640 x 480
	OS Support		5.0 DC 5V	N 720 x 480
	210 MAC OS / XP / Vista / Win 7 / 8 /10		3.3 DC 3.3V	P 720 x 576
	211 MAC OS / XP / Vista / Win 7 / 8 /10			213
	212 MAC OS / XP / Vista / Win 7 / 8 /10			N/A 640 x 480
	213 Win 8.1 / Win 10			HD 1280 x 720