


Specification


Model No.	220LTE	210LTE
Camera Type	Front View	Up View
Pixel Size (μm)	2 x 2	
Image Area (mm)	5.44 x 4.072	
Image Sensor	1/3" CMOS Color	
Dark Signal	4 mV / sec @ 60°C	
Sensitivity	1900 mV / Lux	
S/N Ratio	38.3 dB	
Dynamic Range	64.6 dB	
Lens	4.3 mm / F 2.4	
External Camera Resolution	Digital	1080p / 720p / D1 @ 30 fps (Record) 720p / D1 / CIF @ 30 fps (Preview) 1080p (Photo)
	Analog	D1 / CIF @ 30 fps (Record / Preview) D1 (Photo)
Compression Algorithm	H.264 / H.265 (Video) ; G.726 (Audio)	
File Format	AVI (Video) ; JPG (Photo)	
Video Recording Mode	Standard / Motion	
GPS	GPS / GLONASS	
Storage	128 GB (Micro SD)	
LED Indicator	Power / Link / REC	
Vibration Alert	Power on / off ; REC on / off	
Power Source	DC 5V (Micro USB)	
Power Current	5 W	
Operating Temperature	-10 to 60 Degree C	
Storage Temperature	-40 to 85 Degree C	
App	iOS / Android	
Weight (g)	60	
LTE Band	NA	B17, B5, B4, B2 (United states)
	SA	B28, B5, B8, B3, B1, B7 (South America)
	EU	B20, B5, B8, B3, B1, B7 (Euro)
	AU	B28, B5, B3, B1, B7 (Australia)
	AS	B20, B5, B8, B3, B1, B7 (Asia)
	CA	B20, B5, B8, B3, B1, B7, B39, B40, B41 (China)

* D1 = 720 x 480 * CIF = 320 x 240

220LTE
Front View / With DVR




210LTE
Up View / With DVR



MP-WF210LTE-NA-G

SERIES	FEATURE	DISPLAY	LTE BAND COUNTRY	GPS
MP DVR	WF Wireless	220LTE Front View Color 210LTE Up View Color * LTE 4G Telecommunication	NA United states SA South America EU Euro AU Australia AS Asia CA China	G GPS N/A None

DVR Overview



1. GPS Antenna
2. LTE Antenna
3. Power / Record Key
4. External Control Slot
5. Microphone
6. USB Power Plug
7. SD Card Slot
8. Digital Camera Input
9. SIM Slot
10. Earphone
11. CVBS Video Input
12. SOS Key
- 13~16. LED Indicator