

## Feature

- Operates in 2.4GHz frequency bands compliance of IEEE 802.11b/g/n.
- WEP,TKIP and AES,WPA,WPA2 hardware encryption schemes.
- Analog Camera Input.
- APP operation both on iOS / Android system.



◀ AV100



◀ AV200

## Specification

Model	WF-AV100	WF-AV200
Power Consumption	1.3 W (Max.)	1.7 W (Max.)
Dimension (mm)	54.5 x 28 x 10	72 x 36.6 x 16
Feature	Slim Wi-Fi DVR	Built-in 1100 mAh Rechargeable Li-ion Battery
Color	Black	
Resolution	D1 / 30 fps (Max.)	
Video Input	NTSC / PAL Auto-Detection Standard CVBS Signal camera	
Compression Algorithm	PCM (H.264 / Audio)	
Video File Format	AVI	
Wi-Fi Standard	IEEE 802.11b/g/n 2.4 GHz ISM Band	
Video Recording Mode	Standard / Motion Detection	
Memory Type	Supports up to 64 GB SDHC Micro SD	
Frame Rate	10 / 15 / 20 / 25 / 30 Adjustable	
Time Stamp	YES	
LED Indicator	Power / WI-FI / REC	
Power Input	DC 5V	
APP	iOS / Android	
Weight	55 g	

### ▶ Preview image (android device , IOS device)

1. Download app and install it on android / ios device.

**Android** <https://play.google.com/store/apps/details?id=com.avds.mobilecamp2p>

**IOS** <https://apps.apple.com/tw/app/securepro-plus/id1064009874?l>



SecurePro plus



Android



iOS