

Specification

Spy CCD Camera

SPY CCD CAMERA	
Item NO.	HS-1488x
Video system.	NTSC/PAL
Number of Effective Pixels	510X492(NTSC)
	500X582(PAL)
CCD Image Sensor	1/4" Interline CCD
Scanning System	2:1 INTERLACE
Synchronization	INTERNAL
Resolution (TV Lines)	350 TV LINE
S/N Ratio	more than 48dB
Minimum Illumination	0.5 Lux / F 1.4
Electronic Shutter	1/50 - 1/100000
Horizontal Sync Frequency	NTSC(EIA)-15.73kHz / PAL(CCIR)-15.62kHz
Vertical Sync Frequency	NTSC(EIA)-60kHz / PAL(CCIR)-50kHz
Gamma Consumption	0.45
Video Output	1Vp-p , 75ohms Composite
Audio Output	Frequency 20-16000Hz,S/N ratio more than 63dB SPL(at 1000Hz)(Ordering in advance)
Audio Standard	Frequency 20-16000Hz,S/N ratio more than 58dB
Built-In Lens	3.1mm/F3.4 (3T) , 3.9mm/F3.9 (4T)
Storage Temperature	-30 to 60 Degree C
Working Temperature	-10 to 45 Degree C
Power Source	DC 7-12V(standard)
Power Current	120mA(max)
Cable Dimension (cm)	100



HS-1488U



HS-1488C



HS-1488Y



HS-1488B

Wireless Kit

Ordering Information



AB28814U



BB18814U



HVS-1488U

MODEL	RF Output Power	Frequency	Microphone
AB28814x	200mW	2.4GHz	●
AB68814x	600mW	2.4GHz	●
BB18814x	100mW	1.2GHz	●
BB58814x	500mW	1.2GHz	●
AV28814x	200mW	2.4GHz	
AV68814x	600mW	2.4GHz	
BV18814x	100mW	1.2GHz	
BV58814x	500mW	1.2GHz	

NOTE: **B** **2** **8814** **x**: ① TXT-BOX : A:2.4GHz ; B:1.2GHz
 ② B: W/Microphone ; V: W/O Microphone
 ③ 1: 100mW ; 2: 200mW ; 5: 500mW ; 6: 600mW
 ④ Sunglasses Color

MODEL	PIN HOLE	NOTE
HS-1488C-3T	3.1mm/F3.4	1/4" CCD M.RES
HS-1488B-3T	3.1mm/F3.4	1/4" CCD M.RES
HS-1488U-3T	3.1mm/F3.4	1/4" CCD M.RES
HS-1488Y-3T	3.1mm/F3.4	1/4" CCD M.RES
HS-1488C-4T	3.9mm/F3.9	1/4" CCD M.RES
HS-1488B-4T	3.9mm/F3.9	1/4" CCD M.RES
HS-1488U-4T	3.9mm/F3.9	1/4" CCD M.RES
HS-1488Y-4T	3.9mm/F3.9	1/4" CCD M.RES

NOTE: HS-1488x : **C**: Transparent Type ; **B**: Black Tint
Y: Yellow Tint ; **U**: UV Protection
 <The colors of the sunglasses>
HS-1488C-4T,3T: 4T:3.9mm/F3.9 ; **3T**:3.1mm/F3.4

Other type



HS-1466C
(Frame Glasses)



HS-1466SB
(Frame Glasses)



MRX-1200B
(NEW WIRELESS RECEIVER)



MSR-1200S
(WIRELESS RECEIVER)