


Specification
Dome CCD Camera

CCD DOME CAMERA					
Item NO.		MS- ^C _B 340	MS- ^C _B 640	MS- ^C _B 440	MS- ^C _B 840
Video system.		NTSC/PAL (Color) & EIA/CCIR (B\W)			
Number of Effective Pixels	PAL(CCIR)	500x528	752x582	500x528	752x582
	NTSC(EIA)	510x492	768x494	510x492	768x494
CCD Image Sensor		1/3" Interline CCD		1/4" Interline CCD	
Scanning System		2:1 INTERLACE			
Synchronization		INTERNAL			
Resolution (TV Lines)	COLOR	380	470	350	470
	B\W	420	570	420	570
S/N Ratio		more than 48dB			
Minimum Illumination		0.2Lux / F 1.2 (color) & 0.02Lux / F 1.2 (B\W)			
Electronic Shutter		1/50 - 1/120000 & 1/50 - 1/100000			
Horizontal Sync Frequency		NTSC(EIA)-15.734kHz / PAL(CCIR)-15.625kHz			
Vertical Sync Frequency		NTSC(EIA)-60Hz / PAL(CCIR)-50Hz			
Gamma Consumption		0.45			
Video Output		1Vp-p , 75ohms Composite			
Audio Output		Frequency 20-16000Hz,S/N ratio more than 58dB (Optional)			
Built-In Lens		3.6mm/F2.0			
Lens Angle		3.6mm/92 Degree		3.6mm/70 Degree	
Storage Temperature		-30 to 60 Degree C			
Working Temperature		-10 to 45 Degree C			
Power Source		DC 12V(standard)			
Power Current		150mA(max)			
Dimensions (mm)		MINI 54(W)x45(H)mm			


 MS-C_Bx40x

Dimensions


Unit: mm (Approx)

Other angle lens please inquire for details.

Ordering Information

MODEL	PIN HOLE	MIC	NOTE
MS-C340	3.6mm / F2.0		1/3" CCD M.RES
MS-C640	3.6mm / F2.0		1/3" CCD H.RES
MS-C440	3.6mm / F2.0		1/4" CCD M.RES
MS-C840	3.6mm / F2.0		1/4" CCD H.RES
MS-B340	3.6mm / F2.0		1/3" CCD M.RES
MS-B640	3.6mm / F2.0		1/3" CCD H.RES
MS-B440	3.6mm / F2.0		1/4" CCD M.RES
MS-B840	3.6mm / F2.0		1/4" CCD H.RES
MS-C340A	3.6mm / F2.0	•	1/3" CCD M.RES
MS-C640A	3.6mm / F2.0	•	1/3" CCD H.RES
MS-C440A	3.6mm / F2.0	•	1/4" CCD M.RES
MS-C840A	3.6mm / F2.0	•	1/4" CCD H.RES
MS-B340A	3.6mm / F2.0	•	1/3" CCD M.RES
MS-B640A	3.6mm / F2.0	•	1/3" CCD H.RES
MS-B440A	3.6mm / F2.0	•	1/4" CCD M.RES
MS-B840A	3.6mm / F2.0	•	1/4" CCD H.RES

NOTE:

 1/4" CCD **M.RES.** : **M**: Medium resolution ; **H**: High resolution

 MS-C440**A**: W/Microphone

Feature

- High Quality picture.
- Compact size.
- Mirror function:ordering in advance.
- Microphone Built-in Optional.
- Backlight compensation.
- Auto white balance.
- Equipping Electronics-Auto-Iris.
- Exchange for any kind of lens.
- High speed white balance mode(1Fild).
- High performance.
- Outstanding quality.
- Competitive price.

Other types


MS-C342

 MO-D440
CMOS MINI CAMERA

MS-C446

 MS-B345
Hidden CCD Camera