




Board



MO-B3526G



MO-B3526P-4F



Unit : mm (± 0.5)

Feature

- CCIQ II** ▶ Challenge CCD Image Quality
- Hi Resolution up to 400 TV Lines.
- Compact size.
- Ultra-lightweight!
- Backlight compensation.
- High Quality Picture.
- High Performance.
- Outstanding Quality!
- Day & Night Lens

Specification

Model	MO-B3526G	MO-B3526-4F
Video system	NTSC / PAL	
Number of effective pixels	648 x 488	
Image sensor	1/4" CCIQ II Color Camera	
Resolution(TV Lines)	400 TV Lines	
S/N Ratio	more than 50dB	
Minimum illumination	0.1 LUX / F1.2	
Electronic shutter	60 field/sec (NTSC) , 50 field/sec (PAL)	
Horizontal sync frequency	NTSC(EIA) -15.734kHz , PAL(CCIR) - 15.625kHz	
Vertical sync frequency	NTSC(EIA) - 60Hz , PAL(CCIR) - 50Hz	
Camera consumption	0.45	
Video output	1Vp-p , 75ohm composite	
Storage temperature	-30 to 60 Degree C	
Working temperature	-10 to 45 Degree C	
Built-in Lens	3.7 mm/F2.0	4.3 mm/F2.0
Power source	DC 5~12 V(Standard)	
Power current	50 mA	
Dimension (mm)	22 x 26 (mm)	



MO-B3526G



MO-B3526-4F



MO-B3526-2G

Ordering Information

MODEL	LENS	MIC.	TYPE	MODEL	LENS	MIC.	TYPE
MO-B3526-3C	3.7mm / F2.0	x	CONE	MO-B3526YA-3C	3.7mm / F2.0 Day & Night Lens	External	CONE
MO-B3526-4C	4.3mm / F2.0	x	CONE	MO-B3526YA-4C	4.3mm / F2.0 Day & Night Lens	External	CONE
MO-B3526-3F	3.7mm / F2.0	x	FLAT	MO-B3526YA-3F	3.7mm / F2.0 Day & Night Lens	External	FLAT
MO-B3526-4F	4.3mm / F2.0	x	FLAT	MO-B3526YA-4F	4.3mm / F2.0 Day & Night Lens	External	FLAT
MO-B3526-3T	3.1mm / F3.4	x	SLIM	MO-B3526YA-3T	3.1mm / F3.4 Day & Night Lens	External	SLIM
MO-B3526-4T	3.9mm / F3.9	x	SLIM	MO-B3526YA-4T	3.9mm / F3.9 Day & Night Lens	External	SLIM
MO-B3526G	3.6mm / F2.0	x	G-TYPE	MO-B3526GYA	3.6mm / F2.0 Day & Night Lens	External	G-TYPE
MO-B3526-2G	2.1mm / F2.5	x	G-TYPE	MO-B3526YA-2G	2.1mm / F2.5 Day & Night Lens	External	G-TYPE


MO-B3526GYA **A** : External Mic. MO-B3526GYA **Y** : Day & Night Lens

MO-B3526-2G LENS : 2.1mm/ F2.5(Super Wide-Angle 158°)

Other information

N-1426G

1/4" Color CCD Camera



MO-N3531

1/4" Color CCIQ II Hidden Camera

