

Specification (camera)

Image sensor	1/3" Color CCIQ 960H camera
Video system	NTSC / PAL
Image area(mm)	4.88 x 3.67 (diagonal: 6.1)
Pixel Size(μm)	5.0 x 7.4
Effective pixel	960 x 576
Sensor scan mode	Interlaced
TV lines	710 (NTSC), 740 (PAL)
S/N Ratio	43.3 [dB]
Sensitivity	10.9 [V/Lux.sec]
Dynamic Range	61.8 [dB]
Minimum illumination	0.05 LUX / F1.2
Shutter speed	1/50~1/170,000
Horizontal sync frequency	15.734kHz(NTSC) , 15.625kHz(PAL)
Vertical sync frequency	60Hz(NTSC) , 50Hz(PAL)
Gamma consumption	0.45
Video output	1Vp-p, 75ohms
Lens	4.3mm/F2.0
Focus distance(mm/FID)	infintiy
Storage temperature	-30~60 degree C
Working temperature	-10~45 degree C
Power supply	DC5~12V (80mA)
Dimensions(mm)	11 x 11

Feature ■

- WI-FI smart link design, easy to setup and connect to internet.
- Operates in 2.4GHz frequency bands compliance of IEEE 802.11b/g/n.
- WEP,TKIP and AES,WPA,WPA2 hardware encryption schemes.
- APP operation both on iOS / Android system.
- Built-in 1100mAh rechargeable Li-Lon battery.



WF-C902A-4F

Specification (Wi-Fi DVR)

Resolution	Max D1/30fps
Video Input	NTSC / PAL Auto-Detection, Standard CVBS Signal camera
Compression Algorithm	H.264 / Audio : PCM
Video File Format	AVI
Wi-Fi Standard	IEEE 802.11b/g/n 2.4GHz ISM Band
Video Recording Mode	Standard / Motion Detection
Memory Type	Supports up to 64GB SDHC Micro SD
Frame Rate	10/ 15/ 20/ 25/ 30 Adjustable
Time Stamp	YES
LED Indicator	Power / WI-FI / REC
Power Input	DC 5V
Charge Current	500mA
Power Consumption	Max. 1.7W
Battery Type	Build-in 1100mAh Charge Circuit Li-Lon Battery
Charging Time	2.5 hours
Operating Time	Approx. 130min
APP	iOS / Android
Weight	55g
Dimension	72*36.6*16 mm



Smart Link

Search "SecurePro Plus" or scan the QR code and download it from APP or Android store. Play and install it to your portable. Smart Phone or iPad or Android device.



Connect to the Wi-Fi signal of the actual device



Scan the QR code is on the outside of the device



The device will be added on the list. Click (touch/press) to enter



Input the default password. ("12345678")



Press the home button to Confirm the change



Back to the main page to confirm the internet connection

