

CMOS COLOR CAMERA

Specifications:

	COLOR (MO-R621)	B/W (MO-R321)	B/W (MO-R421)
Video System	PAL/NTSC	CCIR/EIA	CCIR/EIA
Number of Effective Pixels	628X582(PAL)	628X582(CCIR)	352X288(CCIR)
	510X492(NTSC)	510X492(EIA)	320X240(EIA)
Scanning System	2:1 INTERLACE		
Synchronization	INTERNAL		
Resolution (TV Lines)	380 TV LINE		240 TV LINE
S/N Ratio	MORE THAN 48dB		MORE THAN 46dB
Minimum Illumination	3 Lux at F 1.2	0.2 Lux at F 1.2	0.5 Lux at F 1.4
Electronic Shutter	1/50 - 1/15000		1/50 - 1/6000
Horizontal Sync Frequency	PAL 15.625kHz/NTSC 15.734kHz		
Vertical Sync Frequency	PAL 50Hz/NTSC 60Hz		
Gamma Consumption	0.45		
Video Output	1 Vpp , 75 ohms Composite		
Audio Output	NONE		
Built-In Lens	3.6mm/F2.0(G-type)		
Lens Angle	3.6mm/92 Degree	70 Degree	
Storage Temperature	-30 to 60 Degree C		
Working Temperature	-10 to 45 Degree C		
Power Source	DC 7- 12V(standard)		
Power Current	50mA	20mA	

CMOS Color Camera:



MO-RX21

Ordering Information:

MODEL	BOADR LENS	MICROPHONE	NOTE
MO-R621	3.6mm/F2.0		PAL & NTSC
MO-R321	3.6mm/F2.0		CCIR & EIA
MO-R421	3.6mm/F2.0		CCIR & EIA
ANY MODEL CAN BE DIY SET			
Note: KO-RX21 (W/20M CABLE , ADAPTOR)			

Diy Kit



System includes: 20m AV & POWER EXTENSION CABLE, POWER SUPPLY



Security cameras for Surveillance application.