

CMOS HIDDEN CAMERA

Specifications:

	COLOR (MO-D646F)	B/W (MO-D346F)	B/W (MO-D466F)
Video System	PAL/NTSC	CCIR/EIA	CCIR/EIA
Number of Effective Pixels	628X582(PAL)	628X582(CCIR)	352X288(CCIR)
	510X492(NTSC)	510X492(EIA)	320X240(EIA)
Scanning System	2:1 INTERLACE		
Synchronization	INTERNAL		
Resolution (TV Lines)	380 TV LINE		240 TV LINE
S/N Ratio	MORE THAN 48dB		MORE THAN 46dB
Minimum Illumination	3 Lux at F 1.2	0.2 Lux at F 1.2	0.5 Lux at F 1.4
Electronic Shutter	1/50 - 1/15000		1/50 - 1/6000
Horizontal Sync Frequency	PAL 15.625kHz/NTSC 15.734kHz		
Vertical Sync Frequency	PAL 50Hz/NTSC 60Hz		
Gamma Consumption	0.45		
Video Output	1 Vpp , 75 ohms Composite		
Audio Output	Frequency 20-16000Hz,S/N ratio more than 58dB(OPTIONAL)		
Built-In Lens	3.6mm/F2.0(G-type)		
Lens Angle	3.6mm/92 Degree		70 Degree
Storage Temperature	-30 to 60 Degree C		
Working Temperature	-10 to 45 Degree C		
Power Source	DC 7- 12V(standard)		
Power Current	50mA		20mA

Omni Dome Camera:



MO-DX46FA MICRO LENS

Ordering Information:

MODEL	BOADR LENS	MICROPHONE	NOTE
MO-D646F	3.6mm/F2.0		PAL & NTSC
MO-D346F	3.6mm/F2.0		CCIR & EIA
MO-D446F	3.6mm/F2.0		CCIR & EIA
MO-D646FA	3.6mm/F2.0	■	PAL & NTSC
MO-D346FA	3.6mm/F2.0	■	CCIR & EIA
MO-D446FA	3.6mm/F2.0	■	CCIR & EIA

Other angle lens please inquire for details.

Note:KO-DX46X (WITH 20M CABLE , ADAPTOR)

Installation

- DC PLUG FOR POWER INPUT
- RCA female white for audio output
- CH1 RCA female yellow for video output
- CH2 RCA female yellow for video output
- CH3 RCA female yellow for video output
- CH4 RCA female yellow for video output



Tilt Adjustment



Pan Adjustment