

Specification


| NETWORK SERVER | |
|------------------------------|--|
| Model. | IP-001E |
| Power | |
| Supply | DC12V , 1.2A |
| Consumption | -14.4 Watts (max) |
| Networking | |
| Connectivity | 10/100 Ethernet |
| Protocols | SMTP,FTP,DHCP,HTTP |
| Internet | Built-in HTTP Web server, DHCP Client |
| Event Controls | |
| Trigger Source | Motion Detection |
| Alarm Notifications | FTP/Mail motion image, Message |
| Sensor | 1/3" CCD Image Sensor |
| Image | |
| Compression | JPEG/MJPEG |
| Format | NTSC - 640x480 / 320x240 / 160x120 PAL - 704x576 / 352x288 /176x144 |
| Bandwidth Control | Frame Rate Controls |
| Format Rate | 30fps@320x240 25fps@352x288 20fps@640x480 20fps@704x576 |
| Quality | 5 Level image Quality |
| Image adjustments | Brightness / Saturation / Contrast / Hue |
| Security Controls | |
| Access Controls | Administrative / User Level Password Protection |
| Configuration | HTTP Port configurable |
| Log | Historical Access Log Management |
| Operation Environment | |
| Temperature | 5~50 Degree C (41~122 Degree F) |
| Humidity | 20%~80% |
| LED Indications | Power , Network |
| Dimension | 99x163 mm |
| Remote Viewing | Windows 98/2000/XP IE5.X or above |
| Dome Space | |
| Built-in Lens | 6mm/F2.0 |
| View Range | Pan: 360 Degree, Tilt:90 Degree |
| Moving Speed | Per Second 12~300 Degree |
| Dimension | 54 x 30 x 93 (mm) |

Network Server



IP-001E

Dimensions




Unit: mm (Approx)


Other angle lens please inquire for details.

Feature

| |
|--|
| NETWORK IP VIDEO SERVER with 1 Channel |
| IP NETWORK P/T DOME CAMERA. |
| CPU : 32 Bits RISC processor. 16Mb Flash, 64Mb SDRAM |
| Linux OS. |
| TCP/IP network remote Video transmission system. |
| Built-in Web sever. |
| Built-in DHCP Client. |
| Built-in Motion Detection. |



Remote Management



ADSL

10/100Mbps Network