

Specification

Wireless Glasses CCIQ Camera

WIRELESS GLASSES CAMERA		
Model	AD0199116	
Video system	NTSC / PAL	
Number of effective pixels	NTSC(EIA)	510 x 492
	PAL(CCIR)	628 x 582
Image sensor	1/3" CCIQ Camera	
Resolution(TV Lines)	380	
S/N Ratio	more than 48dB	
AGC control	more than +27dB	
Minimum illumination	1 LUX	
Electronic shutter	1/50 - 1/125,000	
Horizontal sync frequency	NTSC(EIA)-15.734kHz / PAL(CCIR)-15.625kHz	
Vertical sync frequency	NTCS(EIA)-60Hz / PAL(CCIR)-50Hz	
Camera consumption	0.45	
Video output	1Vp-p , 75ohm composite	
Audio output	Frequency 20-16,000Hz , S/N ratio more than 58 SPL(at 1000Hz)(Ordering in advance)	
Built-in lens	3.9 mm / F3.9 (4T)	
Lens angle	3.9 mm / 77 Degree	
Power source	DC 9-12V(Standard)	
Power current	60 mA	
Frequency	2.4 GHz 10mW	



AD0199116C

Complete Wireless  
Micro Transmitter & Lithium Ion Rechargeable Battery built-in

Other information




MO-R588



MO-R1612



MO-R1614



MS-1632KJE

1/3" CCD Color Camera  
Automatic Compensation by Digital Noise Reducer



MS-1645

1/3" CCD Color Camera  
Automatic Compensation by Digital Noise Reducer