

Specification

CMOS Camera

CMOS CAMERA	
Item NO.	MO-R806
Video system.	1/6" NTSC / 1/5" PAL
Number of Effective Pixels	306X240(NTSC)
	366X288(PAL)
CMOS Image Sensor	CMOS COLOR CAMERA
Scanning System	2:1 INTERLACE
Synchronization	INTERNAL
Resolution (TV Lines)	240 TV Lines
S/N Ratio	more than 48dB
Minimum Illumination	2 Lux / F 1.2
Electronic Shutter	1/50 - 1/57,000
Horizontal Sync Frequency	NTSC(EIA)-15.734kHz / PAL(CCIR)-15.625kHz
Vertical Sync Frequency	NTSC(EIA)-60Hz / PAL(CCIR)-50Hz
Gamma Consumption	0.45
Video Output	1Vp-p , 75ohms Composite
Audio Output	Frequency 20-16000Hz,S/N ratio more than 58dB SPL(at 1000Hz))(Ordering in advance)
Built-In Lens	2.8 mm / F2.0 Flat type M5.5 Lens
Lens Angle	2.8 mm / 65 Degree
Storage Temperature	-30 to 60 Degree C
Working Temperature	-10 to 45 Degree C
Power Source	DC 9 - 12V
Power Current	35mA(max)




MO-R806

Feature

Dimensions

1/6" NTSC 1/5" PAL CMOS CAMERA
Ultra mini camera (only Ø 8.4 mm)
W/75 ohm 50 CM cable



Other types

 <p>MO-S888 Ultra mini color camera</p>	 <p>MO-S1615P Challenge CCD Image Quality</p>	 <p>MO-S1615G Challenge CCD Image Quality</p>
---	---	---