

Specification

CMOS Dome Camera

Model	MO-D1540	MO-D1640
Video system	NTSC / PAL	
Number of effective pixels	NTSC	656 x 492
	PAL	/
Image sensor	1/4" Color	1/3" Color
Resolution(TV Lines)	380	
S/N Ratio	more than 48dB	
Minimum illumination	1 LUX	
Electronic shutter	1/50 - 1/200,000	1/50 - 1/125,000
Horizontal sync frequency	NTSC-15.734kHz / PAL-15.625kHz	
Vertical sync frequency	NTCS-60Hz / PAL-50Hz	
Camera consumption	0.45	
Video output	1Vp-p , 75ohm composite	
Audio output	Frequency 20-16,000Hz , S/N ratio more than 58 SPL(at 1000Hz)(Ordering in advance)	
Built-in lens	3.6mm / F2.0 (G-type)	
Lens angle	70 °	90 °
Storage temperature	-30 to 60 Degree C	
Working temperature	-10 to 45 Degree C	
Power source	DC 5-12V(Standard)	
Power current	60 mA	
Dimension (mm)	5 x 45	




MO-D1x40

Ordering Information

MODEL	MICRO LENS	Shutter speed	MIC
MO-D1540	3.6mm / F2.0	1/60 ~ 1/125,000	
MO-D1540A		1/60 ~ 1/125,000	
MO-D1640		1/50 ~ 1/200,000	
MO-D1640A		1/50 ~ 1/200,000	

Dimensions



Other type



