

Specification


Snake CCD Camera

CCD SNAKE CAMERA	
Item NO.	SS-1475
Video system.	NTSC/PAL
Number of Effective Pixels	510X492(NTSC) 500X582(PAL)
CCD Image Sensor	1/4" Interline CCD
Scanning System	2:1 INTERLACE
Synchronization	INTERNAL
Resolution (TV Lines)	350 TV LINE
S/N Ratio	more than 48dB
Minimum Illumination	0.2 Lux / F 1.4
Electronic Shutter	1/50 - 1/100000
Horizontal Sync Frequency	NTSC(EIA)-15.734kHz / PAL(CCIR)-15.625kHz
Vertical Sync Frequency	NTSC(EIA)-60Hz / PAL(CCIR)-50Hz
Gamma Consumption	0.45
Video Output	1Vp-p , 75ohms Composite
Built-In Lens	4.0mm/F2.0 (Default focus 15cm)
Storage Temperature	-30 to 60 Degree C
Working Temperature	-10 to 45 Degree C
Power Source	DC 12V(standard)
Power Current	150mA(max)
Dimension(mm)	∅ 16x29(mm) Body : 114x35mm
Cable Dimension(cm)	75 cm



SS-1475

Dimensions



Unit: mm (Approx)

Feature

1/4" CCD CAMERA

SONY COLOR CCD Image Sensor

75cm flexible cable (flexible iron pipe protect) .

4.0mm/F2.0 Built-In Lens (Default focus 15cm)

Other Types



MO-S575

75 ~ 300cm flexible cable (flexible iron pipe protect) .



SS-1461

25cm flexible cable between the mini lens and the slim camera Board
12mm/F2.0 Body Lens