


## Feature

- Focus adjustable (Electronic MF)
- LED Light intensity Adjustable
- Hi Resolution up to 400 TV Lines.
- High Performance.
- Flexible Snake Camera
- LED Light x 4



Unit : mm (± 0.5)

## Specification

Model	MO-V3575V
Video system	NTSC / PAL
Number of effective pixels	648 x 480
Image sensor	1/4" CCIQ II Color Camera
Resolution(TV Lines)	400 TV Lines
S/N Ratio	more than 50dB
Minimum illumination	0.1 LUX / F1.2
Electronic shutter	60 field/sec (NTSC) , 50 field/sec (PAL)
Horizontal sync frequency	NTSC(EIA) - 15.734kHz , PAL(CCIR) - 15.625kHz
Vertical sync frequency	NTSC(EIA) - 60Hz , PAL(CCIR) - 50Hz
Camera consumption	0.45
Video output	1Vp-p , 75ohm composite
Storage temperature	-30 to 60 Degree C
Working temperature	-10 to 45 Degree C
Built-in Lens	3.3 mm / F2.8 (Focus adjustable - Electronic MF)
Power source	DC 6~12 V
Power current	120 mA
Dimension (mm)	LENS:Ø 13.8 (mm) Handle: 280 (mm)



▲MO-V3575V

## Ordering Information

MODEL	LENS	LED LIGHT ILLUMINATION	Image
MO-V3575V	3.3mm / F2.8	5400 LUX	1/4" CCIQ II Color Camera

LED light : white light-standard (IR LED light :940nm or 850nm -ordering in advance)

MO-V3575V V:LED light adjust

MO-V3575V V:Focus adjustable (Electronic MF)

