


Feature

- Hi Resolution up to 400 TV Lines.
- Ultra Lightweight !
- Backlight compensation.
- High Quality Picture.
- High Performance.
- Outstanding Quality !
- Ultra Thin !




Unit : mm (± 0.5)

Specification

Model	MO-S1788-5D
Video system	1/4" CCIQ B/W Camera
Number of effective pixels	EIA (NTSC) Only
Image sensor	656 x 492
Resolution(TV Lines)	400 TV Lines
S/N Ratio	more than 50dB
Minimum illumination	1 LUX / F1.2
Shutter Speed	1/60-1/20,000 Sec.
Horizontal sync frequency	EIA(NTSC) - 15.734kHz
Vertical sync frequency	EIA(NTSC) - 60Hz
Camera consumption	0.45
Video output	1Vp-p , 75ohm composite
Built in - Lens	5.0mm/F3.5
Storage temperature	-30 to 60 Degree C
Working temperature	-10 to 45 Degree C
Power source	DC 5 ~ 12 V(Standard)
Power current	50 mA
Dimension (mm)	8.6 x 8.6 (mm)



MO-S1788-5D



Ordering Information

Model	Lens	Mic.	Model	Lens	Mic.
MO-S1588-5D	5.0mm / F3.5	x	MO-S1588A-5D	5.0mm / F3.5	External
MO-S1788-5D	5.0mm / F3.5	x	MO-S1788A-5D	5.0mm / F3.5	External

Note:

MO-S1588A-5D : 1/4" CCIQ Color Camera

MO-S1788A-5D : 1/4" CCIQ B/W Camera

Other information

N-1426G
1/4" Color CCIQ Camera



MO-B3526G
1/4" CCIQ II Camera

