


Feature

- Hi Resolution up to 400 TV Lines.
- Super Wide Angle
- Compact size.
- Backlight compensation.
- High Quality Picture.
- High Performance.
- Outstanding Quality!



unit : mm (±0.5)

Specification

Model	MO-S3588-2G
Video system	NTSC / PAL
Number of effective pixels	648 x 488
Image sensor	1/4" Color CCIQ II Camera
Resolution(TV Lines)	400 TV Lines
S/N Ratio	more than 50dB
Minimum illumination	0.2 LUX / F1.2
Electronic shutter	60 fps.
Horizontal sync frequency	NTSC(EIA) -15.734kHz , PAL(CCIR) - 15.625kHz
Vertical sync frequency	NTSC(EIA) - 60Hz , PAL(CCIR) - 50Hz
Camera consumption	0.45
Video output	1Vp-p , 75ohm composite
Built-in Lens	Lens:2.1mm/F2.5 micro board lens
Storage temperature	-30 to 60 Degree C
Working temperature	-10 to 45 Degree C
Power source	DC 5~12 V(Standard)
Power current	50 mA
Dimension (mm)	8.6 X 8.6 (mm)



▲ MO-S3588-2G


Ordering Information

Model	Lens	Mic.	Type	Lens (Ø)	Model	Lens	Mic.	Type	Lens (Ø)
MO-S3588-3D	3.9mm / F2.8	x	SLIM	Ø 7	MO-S3588A-3D	3.9mm / F2.8	External	SLIM	Ø 7
MO-S3588-3T	3.1mm / F3.4	x	SLIM	Ø 7	MO-S3588A-3T	3.1mm / F3.4	External	SLIM	Ø 7
MO-S3588-4T	3.9mm / F3.9	x	SLIM	Ø 7	MO-S3588A-4T	3.9mm / F3.9	External	SLIM	Ø 7
MO-S3588-3F	3.7mm / F2.0	x	FLAT	Ø 7	MO-S3588A-3F	4.3mm / F2.0	External	FLAT	Ø 7
MO-S3588-4F	4.0mm / F2.0	x	FLAT	Ø 7	MO-S3588A-4F	4.3mm / F2.0	External	FLAT	Ø 7
MO-S3588-4C	4.0mm / F2.0	x	CONE	Ø 7	MO-S3588A-4C	4.3mm / F2.0	External	CONE	Ø 7
MO-S3588-2G	2.1mm / F2.5	x	Micro board lens	Ø 9	MO-S3588A-2G	2.1mm / F2.5	External	Micro board lens	Ø 9

Note:
MO-S3588A ▶ A : External Microphone

Other Information

MO-S1588-5D
1/4" COLOR CCIQ Camera



MO-R3512
1/4" CCIQ II-Mini Bullet Camera
Waterproof IP 67

