




Board



G-TYPE



PIN HOLE LENS(5F)



Unit : mm (± 0.5)

Feature


- Hi Resolution up to 420 TV Lines.
- Compact size.
- Ultra-lightweight!
- Backlight compensation.
- High Quality Picture.
- Outstanding Quality!

Specification

Model	MS-B328G	MS-B328P
Video system	EIA / CCIR	
Number of effective pixels	510x492(EIA) , 500x528(CCIR)	
Image sensor	1/3" B/W CCD CAMERA	
Resolution(TV Lines)	420 TV Lines	
S/N Ratio	more than 46dB	
Minimum illumination	0.02 LUX / F1.4	
Shutter Speed	1/50-1/100000	
Horizontal sync frequency	NTSC(EIA) -15.734kHz , PAL(CCIR) - 15.625kHz	
Vertical sync frequency	NTSC(EIA) - 60Hz , PAL(CCIR) - 50Hz	
Camera consumption	0.45	
Video output	1Vp-p , 75ohm composite	
Storage temperature	-30 to 60 Degree C	
Working temperature	-10 to 45 Degree C	
Built-in Lens	3.6 mm/F2.0	5.0 mm/F2.0
Power source	DC 12 V(Standard)	
Power current	130 mA	
Dimension (mm)	28 x 28 (mm)	



G-TYPE



PIN HOLE LENS(5F)

Ordering Information

MODEL	LENS	MIC.	TYPE	MODEL	LENS	MIC.	TYPE
MS-B328P-3C	3.7mm / F2.0	x	CONE	MS-B328PA-3C	3.7mm / F2.0	External	CONE
MS-B328P-4C	4.3mm / F2.0	x	CONE	MS-B328PA-4C	4.3mm / F2.0	External	CONE
MS-B328P-3F	3.7mm / F2.0	x	FLAT	MS-B328PA-3F	3.7mm / F2.0	External	FLAT
MS-B328P-4F	4.3mm / F2.0	x	FLAT	MS-B328PA-4F	4.3mm / F2.0	External	FLAT
MS-B328P-3T	3.1mm / F3.4	x	SLIM	MS-B328PA-3T	3.1mm / F3.4	External	SLIM
MS-B328P-4T	3.9mm / F3.9	x	SLIM	MS-B328PA-4T	3.9mm / F3.9	External	SLIM
MS-B328G	3.6mm / F2.0	x	G-TYPE	MS-B328GA	3.6mm / F2.0	External	G-TYPE

Note:

- MS-B328GA A : External Mic.
MS-B328GA Medium Resoulution 1/3" CCD B/W Camera

Other information

NX-1426G

1/4" Color CCD star-light Camera

