




**Board**



**MO-B8019-3D**



**MO-B8019-3T**




Unit : mm (± 0.5)

**Feature**


- Hi Resolution up to 380 TV Lines.
- Compact size.
- Ultra-lightweight!
- Backlight compensation.
- High Quality Picture.
- High Performance.
- Outstanding Quality!
- Day & Night Lens

**Specification**

Model	MO-B8019-3D	MO-B8019-3T
Video system	NTSC / PAL	
Number of effective pixels	640 x 480 (NTSC & PAL)	
Image sensor	1/4" CCIQ Color Camera	
Resolution(TV Lines)	380 TV Lines	
S/N Ratio	more than 50dB	
Minimum illumination	0.3 LUX / F1.2	
Image Transfer Rate	60 fps	
Horizontal sync frequency	NTSC(EIA) -15.734kHz , PAL(CCIR) - 15.625kHz	
Vertical sync frequency	NTSC(EIA) - 60Hz , PAL(CCIR) - 50Hz	
Camera consumption	0.45	
Video output	1Vp-p , 75ohm composite	
Storage temperature	-30 to 60 Degree C	
Working temperature	-10 to 45 Degree C	
Built-in Lens	3.9mm/F2.8	3.1mm/F3.4
Power source	DC 3.3 V(Standard)	
Power current	120 mA	
Dimension (mm)	19 x 22 x 7.9 (mm)	19 x 22 x 8.8(mm)



MO-B8019-3D



MO-B8019-3T

**Ordering Information**


MODEL	LENS	MIC.	TYPE	MODEL	LENS	MIC.	TYPE
MO-B8019-3C	3.7mm / F2.0	x	CONE	MO-B8019YA-3C	3.7mm / F2.0 Day & Night Lens	External	CONE
MO-B8019-4C	4.3mm / F2.0	x	CONE	MO-B8019YA-4C	4.3mm / F2.0 Day & Night Lens	External	CONE
MO-B8019-3F	3.7mm / F2.0	x	FLAT	MO-B8019YA-3F	3.7mm / F2.0 Day & Night Lens	External	FLAT
MO-B8019-4F	4.3mm / F2.0	x	FLAT	MO-B8019YA-4F	4.3mm / F2.0 Day & Night Lens	External	FLAT
MO-B8019-3T	3.1mm / F3.4	x	SLIM	MO-B8019YA-3T	3.1mm / F3.4 Day & Night Lens	External	SLIM
MO-B8019-4T	3.9mm / F3.9	x	SLIM	MO-B8019YA-4T	3.9mm / F3.9 Day & Night Lens	External	SLIM
MO-B8019-3D	3.9mm / F2.8	x	SLIM	MO-B8019YA-3D	3.9mm / F2.8 Day & Night Lens	External	SLIM
MO-B8019G	3.6mm / F2.0	x	G-TYPE	MO-B8019GYA	3.6mm / F2.0 Day & Night Lens	External	G-TYPE

Note:


MO-B8019GYA **A** : External Mic. MO-B8019GYA **Y** : Day & Night Lens

**Other information**


N-1426G  
1/4" Color CCD Camera




MO-N3526  
1/4" Color CCIQ II Camera






**Board**



**MO-B3526G**



**MO-B3526P**



Unit : mm (± 0.5)

**Feature**

- CCIQ II** ▶ Challenge CCD Image Quality
- Hi Resolution up to 400 TV Lines.
- Compact size.
- Backlight compensation.
- High Quality Picture.
- High Performance.
- Outstanding Quality!
- Competitive Price!

**Specification**

Model	MO-S3526G	MO-S3526-4F
Video system	NTSC / PAL	
Number of effective pixels	648 x 488	
Image sensor	1/4" CCIQ II Color Camera	
Resolution(TV Lines)	400 TV Lines	
S/N Ratio	more than 48dB	
Minimum illumination	0.1 LUX / F1.2	
Electronic shutter	60 fps.	
Horizontal sync frequency	NTSC(EIA) -15.734kHz, PAL(CCIQ) - 15.625kHz	
Vertical sync frequency	NTSC(EIA) - 60Hz, PAL(CCIQ) - 50Hz	
Camera consumption	0.45	
Video output	1Vp-p, 75ohm composite	
Storage temperature	-30 to 60 Degree C	
Working temperature	-10 to 45 Degree C	
Built-in Lens	3.7 mm/F2.0	4.3 mm/F2.0
Power source	DC 5~12 V(Standard)	
Power current	100 mA	
Dimension (mm)	22 x 26 x 28 (mm)	22 x 26 x 17 (mm)



MO-S3526-4F



MO-S3526G

**Ordering Information**

Model	Lens	Mic.	Model	Lens	Mic.
MO-S3526-3C	3.7mm / F2.0	x	MO-S3526A-3C	3.7mm / F2.0	Built-in
MO-S3526-4C	4.3mm / F2.0	x	MO-S3526A-4C	4.3mm / F2.0	Built-in
MO-S3526-3F	3.7mm / F2.0	x	MO-S3526A-3F	3.7mm / F2.0	Built-in
MO-S3526-4F	4.3mm / F2.0	x	MO-S3526A-4F	4.3mm / F2.0	Built-in
MO-S3526-5F	5.0mm / F2.2	x	MO-S3526A-5F	5.0mm / F2.2	Built-in
MO-S3526-3T	3.1mm / F3.4	x	MO-S3526A-3T	3.1mm / F3.4	Built-in
MO-S3526-4T	3.9mm / F3.9	x	MO-S3526A-4T	3.9mm / F3.9	Built-in
MO-S3526-4T	3.9mm / F3.9	x	MO-S3526A-4T	3.9mm / F3.9	Built-in

**Note:**

MO-S3526Y : Day & Night

**Other information**

**CCIQ II HIDDEN CAMERA ▶ MO-N35310**

