


**Feature**

- High Sensitivity!
- High Performance.
- 1/8" CCIQ II Color
- Ø 4.8 mm only
- 656 x 496 Pixel

**Specification**

unit : mm (±0.5)

Model	MO-B0804P	MO-B0804PK
Pixel size	2.8 um x 2.8um	
Effective Image Area	1.837 mm x 1.389 mm	
Video system	NTSC / PAL	
Number of effective pixels	656 x 496 (NTSC & PAL)	
Image sensor	1/8" CCIQ II Color Camera	
Resolution(TV Lines)	400 TV Lines	
S/N Ratio	41.6 dB	
Dynamic range	56.4 dB	
Sensor scan mode	progressive scan	
Minimum illumination	1LUX / F1.2	
Max. Frame Rate	30 fps.	15 fps.
Sensitivity	0.94V /Lux.sec	
Horizontal sync frequency	NTSC -15.734kHz , PAL - 15.625kHz	
Vertical sync frequency	NTSC - 60Hz , PAL - 50Hz	
Camera consumption	0.45	
Video output	1Vp-p , 75ohm composite	
Built - lens	1.88mm/ F2.8	
Storage temperature	-30 to 60 Degree C	
Working temperature	-10 to 45 Degree C	
Power source	DC 3.3~5V	
Power current	130 mA(max)	
Dimension (mm)	(D) 4.8 (mm)	



MO-B0804P

**Order information**

MODEL	LED	Max. Frame Rate	Built-in Lens
MO-B0804	W/O LED Light	30 fps.	W/O LENS
MO-B0804K	W/O LED Light	15 fps.	W/O LENS
MO-B0804P	W/O LED Light	30 fps.	1.88mm/F2.8
MO-B0804PK	W/O LED Light	15 fps.	1.88mm/F2.8
MO-B0804LP	LED x 4	30 fps.	1.88mm/F2.8
MO-B0804LPK	LED x 4	15 fps.	1.88mm/F2.8
MO-B0804LP	L: W/O LED x 4		

**Other information**

**MO-B1003**

- 1/10" CCIQ II
- Lens : 2.5 mm Only !!

1/10" Color CCIQ II Camera  
Pixel : 400 x 400 (NTSC / PAL )  
3300mV/Lux  
Sensor board:(D)2.5 x 5 (mm)  
+  
Main board: 70 x 15(mm)

