

Feature

- Hi Resolution up to 480 TV Lines.
- Backlight compensation.
- High Quality Picture.
- Waterproof IP67
- Outstanding Quality!
- Competitive Price!

Specification

UNIT:±0.5mm


Model	ED-3005
Video system	NTSC / PAL
Number of effective pixels	728(H) x 488(V)
Image sensor	1/3" Color Endoscope Camera
Resolution(TV Lines)	480 TV Lines
S/N Ratio	more than 46.4 dB
Minimum illumination	0.05Lux F# 1.2 20IRE
Frame Rate	60 fps (NTSC) , 50 fps (PAL)CVBS
Horizontal sync frequency	NTSC(EIA) -15.734kHz , PAL(CCIQ) - 15.625kHz
Vertical sync frequency	NTSC(EIA) - 60Hz , PAL(CCIQ) - 50Hz
Sensitivity	13.8 V/Lux.sec
Dynamic Range	63.7 [dB]
Camera consumption	0.45
Video output	1Vp-p , 75ohm composite
Storage temperature	-30 to 60 Degree C
Working temperature	-10 to 45 Degree C
Built-in Lens	3.6mm/ F6.0
Focus distance	5 cm
LED	white LED x 10
Power source	DC 5~12 V
Power current	100 mA
Dimension (mm)	Ø11 X 36



ED-3005

Perfect for

1. Inspection: pipeline, sewage, air duct, machine
2. Disaster Rescue: earthquake, tornado, hurricane, snow avalanche, fire, flood
3. Insurance Claim Adjuster: inspect property damage, vehicle damage.
4. Medical Endoscope.



other information

MO-L805

1/18" (NTSC) Color CMOS Camera
 Pixels : 76800 Pixel
 Lens : 0.96 mm / F2.8
 Dimension : diameter- 5mm

