



MD-T5015LV-3828



MD-L5015V-3828



UNIT:±0.5mm

Feature

- 5.0 MegaPixel USB QSXGA!
- High sensitivity!
- High performance.
- Full HD image pixel
- Waterproof IP67

Specification



Model	MD-T5015LV-3828
Max. frame rate	<ul style="list-style-type: none"> • Full 5.0M 2592 x 1944 /15 fps , • FHD 1920 x 1080 /30 fps , • HD 1280 x 720 /60 fps , • VGA 640 x 480 /60 fps
pixel size	1.4um x 1.4um
Image sensor	1/4" CCIQ III digital qsxga cmos camera module
Image area	3.651 x 2.744mm
Scan mode	progressive
Sensitivity	Sensitivity 5100 e-/lux.sec
Dynamic range	63 dB
UVC format	MJPEG
Storage temperature	-40~85 Degree C
Working temperature	0~70 Degree C
Built-in lens	f 3.87mm /F 2.8
LED	White LED x 10
Interface	USB 2.0 (Compliant with USB Video Class 1.1 standard)
Output format	RAW 10Bit
Operating system	Windows XP, Windows 7, Windows 8, Mac OS, Windows10 (Windows 7 operating system in use, you need to install MJPG decoders.)
Power source	DC 5V (USB)
Power current	I:250 mA I _{sb} :50 mA
Dimension(mm)	Ø 15 x 41 mm



MD-T5015LV-3828



MD-L5015V-3828



Computer