



Unit : mm (± 0.5)

**Feature**

- Compact size.
- High Performance.
- Outstanding Quality!
- Competitive Price!



**Specification**

Model	ED-SL1078
Video system	NTSC / PAL
Number of effective pixels	400 x 400
Image sensor	1/10" CCIQ II Color Camera
LED Light	white light LED x4
Resolution(TV Lines)	300 TV Lines
S/N Ratio	more than 50dB
Scan mode	progressive
Minimum illumination	2Lux /F3.4
Frame rate	30 fps
Horizontal sync frequency	NTSC(EIA) -15.734kHz , PAL(CCIR) - 15.625kHz
Vertical sync frequency	NTSC(EIA) - 60Hz , PAL(CCIR) - 50Hz
Camera consumption	0.45
Video output	1Vp-p , 75ohm composite
Storage temperature	-30 to 60 Degree C
Working temperature	-10 to 45 Degree C
Power source	DC 5~12V
Power current	250 mA-max
Dimension (mm)	Ø7.8 x 30

<b>ED-</b>	<b>SL</b>	<b>1</b>	<b>078</b>	<b>-120</b>
	<b>SL:</b> Side view	<b>1:</b> white LED	<b>078:</b> Ø7.8mm	<b>120:</b> 120 degree lens
	<b>TL:</b> Front view	<b>8:</b> IR 850nm LED		
		<b>9:</b> IR 940nm LED		
note		with LED power switch	tube diameter's size can be customized	