


**MD-B5026-3.0**

**MD-B5026V-4528**



**Feature**

- 5.0 MegaPixel USB QSXGA!
- High Sensitivity!
- High Performance.
- Full HD image pixel

**Specification**



Model	MD-B5026-3.0	MD-B5026V-4528
Max. Frame rate	<ul style="list-style-type: none"> <li>● Full 5.0M 2592 x 1944 /15 fps ,</li> <li>● FHD 1920 x 1080 /30 fps ,</li> <li>● SXGA 1280 X 960 /30 fps ,</li> <li>● HD 1280 x 720 /60 fps ,</li> <li>● VGA 640 x 480 /60 fps</li> </ul>	
Pixel size	1.4um x 1.4um	
Image sensor	1/4" CCIQ III DIGITAL QSXGA CMOS Camera module	
Image area	3.651 x 2.744mm	
Scan mode	progressive	
Sensitivity	Sensitivity 5100 e-/lux.sec	
Dynamic range	63 dB	
UVC format	MJPEG	
Storage temperature	-30 to 60 Degree C	
Working temperature	-10 to 45 Degree C	
Built-in Lens	f 3.0 /F2.0	f 4.5 /F 2.8 (auto focus)
View angle	H= 62° 19'; V= 48° 48'; D= 74° 14'	H= 43° 55'; V= 33° 39'; D= 53° 32'
Interface	USB 2.0 (Compliant with USB Video Class 1.1 standard)	
Output format	RAW 10Bit	
Operating system	Windows 7, Windows 8 (WINDOWS 7 operating system in use, you need to install MJPG decoders.)	
Power source	DC 5V (USB)	
Power current	I:170 mA ; ISB:50 mA	I:250 mA; ISB:50 mA
Dimension(mm)	22 x 26 x 25.6mm	22 x 26 x 7.9mm
White balance	AUTO	
Gain control	AUTO	
Exposure	AUTO	




MD-B5026-3.0




MD-B5026V-4528





**MD-B5026-3.0**

**MD-B5026V-4528**



**Feature**

- 5.0 MegaPixel USB QSXGA!
- High Sensitivity!
- High Performance.
- Full HD image pixel

**Specification**



Model	MD-B5026-3.0	MD-B5026V-4528
Max. Frame rate	<ul style="list-style-type: none"> <li>● Full 5.0M 2592 x 1944 /15 fps ,</li> <li>● FHD 1920 x 1080 /30 fps ,</li> <li>● SXGA 1280 X 960 /30 fps ,</li> <li>● HD 1280 x 720 /60 fps ,</li> <li>● VGA 640 x 480 /60 fps</li> </ul>	
Pixel size	1.4um x 1.4um	
Image sensor	1/4" CCIQ III DIGITAL QSXGA CMOS Camera module	
Image area	3.651 x 2.744mm	
Scan mode	progressive	
Sensitivity	Sensitivity 5100 e-/lux.sec	
Dynamic range	63 dB	
UVC format	MJPEG	
Storage temperature	-30 to 60 Degree C	
Working temperature	-10 to 45 Degree C	
Built-in Lens	f 3.0 /F2.0	f 4.5 /F 2.8 (auto focus)
View angle	H= 62° 19'; V= 48° 48'; D= 74° 14'	H= 43° 55'; V= 33° 39'; D= 53° 32'
Interface	USB 2.0 (Compliant with USB Video Class 1.1 standard)	
Output format	RAW 10Bit	
Operating system	Windows 7, Windows 8 (WINDOWS 7 operating system in use, you need to install MJPG decoders.)	
Power source	DC 5V (USB)	
Power current	I:170 mA ; ISB:50 mA	I:250 mA; ISB:50 mA
Dimension(mm)	22 x 26 x 25.6mm	22 x 26 x 7.9mm
White balance	AUTO	
Gain control	AUTO	
Exposure	AUTO	



MD-B5026-3.0



MD-B5026V-4528



Computer