

Feature

- Hidden Camera
- High performance.
- Full HD image pixel
- Multifunction glasses: Reading glasses and Spy glasses. The most inconspicuous glasses camera just looks like everyday glasses.

UNIT:±0.5mm

Specification



Model	HS-1600FDC-77	HS-1200FDC-77
Built- in microphone	Built- in microphone	N/A
Max. frame rate	1920x1080@ 30fps MJPG/ 3fps YUV 1280x720@ 30fps MJPG/ 12fps YUV 640x480@ 30fps MJPG/ 30fps YUV 320x240@ 30fps MJPG/ 30fps YUV	
Image sensor	1/6" Digital CMOS Camera	
Image area	2.7288x1.5498mm	
Built-in Lens	1.83mm/F2.0	
View angle	H= 70°; V= 42.7°; D= 77.3°	
pixel size	1.4 μm x 1.4 μm	
Scan mode	progressive	
Sensitivity	553 mV/(Lux-sec)	
Dynamic range	73.3 dB @ 15.5x gain	
UVC format	MJPEG, YUY2	
Storage temperature	-30 to 60 Degree C	
Working temperature	-10 to 45 Degree C	
Interface	USB 2.0 (Compliant with USB Video Class 1.1 standard)	
Operating system	Windows XP, windows Vista, window 7, windows 8	
Power source	DC 5V (Micro USB OTG B type)	
Power current	160mA	
Dimension(mm)	160x150	

HS-1600FDC-77



1 CONNECTOR		2 CAMERA TYPE		3 Resolution		4 Angle (Lens)	
HSD	USB 2.0 A type	1200	no microphone	FDC	1080p (Full HD)	77	77°
HS	Micro USB OTG B type	1600	Built- in microphone	HDC	720p (HD)	58	58°
HST	USB type-C			VGC	VGA	34	34°
				1080p (Full HD) 1920x1080@ 30fps MJPG/ 3fps YUV 1280x720@ 30fps MJPG/ 12fps YUV 640x480@ 30fps MJPG/ 30fps YUV 320x240@ 30fps MJPG/ 30fps YUV 720p (HD) 1280x720@ 30fps MJPG/ 12fps YUV 640x480@ 30fps MJPG/ 30fps YUV 320x240@ 30fps MJPG/ 30fps YUV VGA 640x480@ 30fps MJPG/ 30fps YUV 320x240@ 30fps MJPG/ 30fps YUV		Built-in Lens: 1.83mm/F2.0 FOV 77° angle only have 1080p resolution FOV 58° angle only have 720p resolution FOV 34° angle only have VGA resolution	

User can adjust brightness, Gamma, white balance, Exposure Time, Sharpness, Backlight Compensation, Hue, Saturation, Mirror, Flip, Frame Rate, Resolution, and AWB.



Other information


- Wireless/WiFi (Transmitter)
- Resolution: 1280x720, 640x480 @30fps
 - Transmission distance: 5-30m
 - Wireless frequency: 3.412G~2.462G
 - Image format: MJPG
 - Video format: avi
 - System requirement: iOS/Android/Windows
 - Power output: DC5V (micro USB for camera)
 - Battery Capacity: 850mAh (include)
 - Dimensions(mm): 62(L) x 35(W) x 17(H)

▼MST-WF16N



- Wi-Fi
- FTP
- Internet
- UVC Camera
- Loop Record
- H.264 MJPG Video Format
- 128GB Micro SD
- RTC Function
- APP Preview


Extremely lightweight 1/6" CMOS UVC glasses camera with 1920x1080 (1080p) resolution. Compatible with mini UVC Wi-Fi DVR. Supports H.264 & MJPG video format input, loop recording, snapshot functions. Supports max memory 128GB(micro SD). Users can view live streaming video via a smartphone.



Model: HS-1600FDC



Micro SD Slot (support 128GB)



Model: MP-WF580K-MM