



Body Type


3C Lens



3F Lens



3T Lens



unit : mm (±0.2)

Feature

- High Sensitivity!
- High Performance.
- 1/4" CCIQ IV Color
- Compact size

Specification

Model	MO-S7510
Video system	NTSC / PAL
Number of effective pixels	648(H) x 488(V) (NTSC & PAL)
Effective Image Area	3.63 mm x 2.73 mm x 4.54 mm
Pixel Size	5.6 um x 5.6 um
Image sensor	1/4" Color CCIQ IV Camera
Resolution(TV Lines)	500 TV Line(NTSC), 560 TV Line(PAL)
S/N Ratio	46.2 [dB]
Dynamic range	65.3 [dB]
Minimum illumination	0.05Lux at F1.2 20IRE
Frame Rate	NTSC: 60 field / sec, PAL: 50field / sec
Sensitivity	10.5 [V/Lux.sec]
Horizontal sync frequency	NTSC -15.734kHz , PAL - 15.625kHz
Vertical sync frequency	NTSC - 60Hz , PAL - 50Hz
Camera consumption	0.45
Video output	1Vp-p , 75ohm composite
Storage temperature	-30 to 60 Degree C
Working temperature	-10 to 45 Degree C
Power source	Camera input: DC 5~12V
Power current	80 mA(max)-DC 12V
Dimension (mm)	11 x 11 mm ±0.2mm



MO-S7510-3C



MO-S7510-3F



MO-S7510-3T

Other information

Model	Built-in Lens
MO-S7510-3C	3.7mm/F2.0
MO-S7510-4C	4.3mm/F2.0
MO-S7510-3F	3.7mm/F2.0
MO-S7510-4F	4.3mm/F2.0
MO-S7510-3T	3.1mm/F3.4
MO-S7510-4T	3.9mm/F3.9
MO-S7510-3G	3.6mm/F2.0
MO-S7510-3D	3.9mm/F2.8
MO-S7510-4G	4.0mm/F1.2
MO-S7510-3GS	3.6mm/F2.0
MO-S7510-121	1.21mm/F2.0
MO-S7510-139	1.39mm/F2.0

Note:

MO-S7510^A

^A: with Microphone