



## Specification

Model	L26930IR-M5.5-53
Filter type	IR cut $650 \pm 10$ nm
Sensor type	1/4"
EFL (mm)	2.63mm
Aperture F/no	3.0
Image Circle	$\phi 5.0$ mm
Back Focal Length	$3.66 \text{mm} \pm 5\%$ (in air)
Field Angle (D x H x V)	$143^\circ : 95.6^\circ : 67.4^\circ$
Total Track	13.35mm
Mount	M5.5 x P0.35
Diameter of lens (mm)	$\phi 6.5 \times 10$
TV Distortion	$< -35.95\%$

\*NO Lens holder