

Feature ■

- Support micro SD 32GB, Live streaming preview, Loop recording
- Playback via FTP, Hidden camera series

Specification

Product Image	Calcuator	Book	Bag	Table clock	Wall clock	Hat
Model	WF-C411HD	WF-C409HD	WF-C410HD	WF-C468HD	WF-C462HD	WF-C402HD
Chipset	ABC8000, 1Ghz MIPS, MCU					
Standards	IEEE 802.11 n/b/g standards compliant					
RF interface	i-PEX connector x1 & PCB antenna x1					
Operating Frequency	2.412 - 2.483GHz(Subject to Local Regulations) Frequency Range USA (FCC): 2.412GHz ~ 2.462GHz Europe (ETSI): 2.412GHz ~ 2.472 GHz Japan (TELEC): 2.412GHz ~ 2.483GHz					
Data Rate	802.11b: 1, 2, 5.5, 11Mbps 802.11g: 6, 9, 12, 18, 24, 36, 48, 54Mbps 802.11n: up to 300Mbps					
Bandwidth, Channels	802.11n 20MHz/40MHz ;802.11b/g USA (FCC) 11 channels; EU (ETSI) 13 channels; Japan (TELEC) 13 channels					
Transmit Power	802.11b: 16+/-1.5dBm@11Mbps 802.11gn HT20: 13+/-1.5dBm@MCS7 802.11gn HT40: 13+/-1.5dBm@MCS7 802.11n HT20: 13+/-1.5dBm@MCS7 802.11n HT20: 13+/-1.5dBm@MCS7					
Receive Sensitivity	11n: ≤ -67 dBm typical with 20MHz ≤ -64 dBm typical with 40MHz 11g: ≤ -71 dBm typical @ 54Mbps 11b: ≤ -82 dBm typical @ 11Mbps					
Function	loop recording					
Video format	H.264, MJPEG, (UVC camera)					
Resolution	1280 x 720 HD 720P, 25FPS					
Lens	4.0mm/F2.0					
Operating Voltage	5V/ 1A (5V/520mA)					
Local Storage	Support micro SD 32GB					
Operating	0~40°C. 10% to 90% Non-Condensing					
Storage	-30 ~ 70°C. 10% to 95% Non-Condensing					

APP

User can adjust camera parameter according to different environment.

Easy Preview

Function