


**Feature**

- High Sensitivity!
- High Performance.
- UVC Rigid Camera
- Ø 5.9 mm only
- 1280x720 resolution
- Light source adjustable



**Specification**

Model	EDD-SL20959L
	Color
Max. frame rate	1280x720@ 30fps MJPG/ 10fps YUV
Pixel size	1.4 μm x 1.4 μm
Image sensor	1/9" Digital CMOS Camera Module
Image area	1.819 x1.033 mm
Scan mode	progressive
Sensitivity	585mV/Lux-sec
Dynamic range	68.4dB @16x gain
UVC format	MJPEG, YUY2
Storage temperature	-30 to 60 Degree C
Working temperature	-10 to 45 Degree C
Interface	USB 2.0 (Compliant with USB Video Class 1.1 standard)
Shutter	rolling shutter
Operating system	Windows XP, Windows Vista, Window 7, Windows 8
Power source	DC 5V (USB/with power board)
Power current	170mA
Dimension(mm)	Ø5.9



**More Information**

<b>EDD-</b>	<b>SL-</b>	<b>209</b>	<b>59</b>	<b>L</b>	<b>-90</b>
<b>EDD:</b> USB A	<b>SL:</b> Side view	sensor	<b>59:</b> Ø5.9mm	<b>L:</b> white LED	<b>76:</b> 76 degree lens
<b>EDM:</b> Micro USB	<b>TL:</b> Front view			<b>L8:</b> IR 850nm LED	<b>90:</b> 95 degree lens
<b>EDT:</b> USB C				<b>L9:</b> IR 940nm LED	<b>120:</b> 120 degree lens
			tube diameter's size can be customized	LED power switch	

**other Information**



**UHD-DC 02E-Y**

- UVC HDMI android stick
- OS support: Android KitKat 4.4.2
- Function: Miracast, mirror phone or tablet to TV, Gaming, Browser, Email, YouTube, Netflix
- Dimensions(mm): 66.5 x 30.5 x 13



**MST-WF16N**

- Resolution: 1280x720, 640x480 @30fps
- Transmission distance: 5-30m
- Image format: MJPG
- Dimensions(mm): 62 x 35 x 17