



Unit: mm

Specification

Model	L2125AR-M12
Sensor type	1/3", 1/4"
Field Angle (D/H/V)	1/3" D=170°, 1/4" D=121.8°
Image circle	6.0mm
EFL	2.1mm
FBL	6.59mm \pm 0.3mm
TTL	24.8mm \pm 0.4mm
Aperture F/no	2.5
Mount	M12 x P0.5

*NO Lens holder