



Unit: mm

Specification

Model	L21261R-M5.5
Sensor type	1/4"
Field Angle	H= 132°; V= 107°; D= 152° (PC7080)
Filter type	T50%=IR 655nm
EFL (mm)	2.12mm
Aperture F/no	2.6
Total track of an Optic	11.81mm
Lens Construction	2AP 3G
Mount	M5.5 x P0.35
Diameter of lens (mm)	ø 5.5 x 10.2
Optical distortion	-64.3%@Ø4.48

*NO Lens holder