

Specification

Model	L21633IR-M5.5
Filter type	IR cut 650±10nm
Sensor type	1/4"
EFL (mm)	2.16mm
Aperture F/no	3.3
Image Circle	Ø5.1mm
Back Focal Length	3.32mm (Tol: ±0.2mm, in air)
Field Angle (D x H x V)	150° : 92° : 66.4°
Total Track	13.35mm
Mount	M5.5 x P0.35
Diameter of lens (mm)	ø 6.5x10
TV Distortion	< -39.1%

*NO Lens holder

There are camera apply to lens

Model	Image Circle	Image Sensor	Pixel Size	Resolution	Size(mm)
MO-B3506	4.5mm	1/4" color	5.55 x 5.55um	648 x 488	7.7(D)
MO-B5407	3.43mm	1/5" color	4.2 x 4.2um	640 x 480	(D)7
MO-B6107	3.86mm	1/7" color	1.75 x 1.75um	720 x 480	(D)7


NOTE :



MO (Mini 4pin(male))



MQ (Waterproof 4pin(male))



MJ (Ø2.5mm phone plug)

G : GND
A : AUDIO
P : DC POWER
V : VIDEO