

















Image	Model	EFL (mm) Aperture F No.	Mount Thread	Filter	Sensor	Image Circle (mm)	Chief Ray Angle	Field Angle (D x H x V)	Total Track (mm)	Diameter (mm)	TV Distortion	Lens Construction	Note
	L09520IR-M7-01	0.95mm / F 2.0	M 7 × P 0.35	IR	1/4"	Ø 5.12	< 19°	D: 160° H: 120° V: 100°	15.75	-	<- 8.5%	4E + IR	
	L12920IR-M12	1.29 mm / F 2.0	M 12 × P 0.5	IR	1/2.9"	Ø 5.8	< 21.2°	D: 205° H: 190° V: 113°	15.11	16.5 (D) × 12.98	-	1G5P + IR	
	L13924IR-M10	1.39 mm / F 2.4	M 10 × P 0.6	IR	1/4"	Ø 5.13	-	D: 141° H: 119° V: 96°	-	13 (D) × 8.65	<- 26.8 %	3 Component 4 Element	
	L12050IR-M12	12 mm / F 5.0	M 12 × P 0.5	IR	1/3"	-	15°	D: 22.67°	-	12 (D) × 13.69	- 0.25 %	3G	
Coming Soon	L1653	16 mm / F 5.3	M 12 × P 0.5	AR	1/4"	-	-	D: 16.2° H: 9.5° V: 15.8°	23.35	-	-0.15 % @ 13"	3	
	L2110LIR-M5.5-52	2.1 mm / F 10	M 5.5 × P 0.35	AR	1/4"	5.12	24.6°	D: 125° H: 96° V: 72°	-	-	-	2P 3G	
	L2125AR-M12	2.1 mm / F 2.5	M 12 × P 0.5	IR	1/4"	6	-	D: 121.8°	24.8	-	-	-	
	L2125L9AR-M5.5-52	2.1 mm / F 2.5	M 5.5 × P 0.35	IR	1/4"	5.12	-	D: 125° H: 96° V: 72°	-	-	-	2P 3G	
	L2125L8AR-M5.5-52	2.1 mm / F 2.5	M 5.5 × P 0.35	IR	1/4"	5.12	-	D: 125° H: 96° V: 72°	-	-	-	2P 3G	
	L2126IR-M5.5	2.12 mm / F 2.6	M 5.5 × P 0.35	IR	1/4"	3.6	-	D: 152° H: 132° V: 107°	11.81	5.5 (D) × 10.2	-	2AP 3G	
	L2125IR-M5.5-50	2.14 mm / F 2.5	M 5.5 × P 0.35	IR	1/4"	5.12	-	D: 125° H: 96° V: 72°	11.81	6.5 (D) × 9.07	-	-	



















Image	Model	EFL (mm) Aperture F No.	Mount Thread	Filter	Sensor	Image Circle (mm)	Chief Ray Angle	Field Angle (D x H x V)	Total Track (mm)	Diameter (mm)	TV Distortion	Lens Construction	Note
	L2110IR-M5.5-52	2.149 mm / F 10	M 5.5 × P 0.35	IR	1/4"	4.5 mm	-	D: 125° H: 96° V: 72°	11.69	6.5 (D) × 9.57	-	-	
	L21526IR-M5.5	2.15 mm / F 2.6	M 5.5 × P 0.35	IR	1/4"	4.5 mm	-	D: 125° H: 96° V: 72°	-	-	-	2P3G + IR Filter	
	L21633IR-M5.5	2.16 mm / F 3.3	M 5.5 × P 0.35	IR	1/4"	5.1 mm	-	D: 150° H: 92° V: 66.4°	13.35	6.5 (D) × 10	<- 39.1%	5G + IRF	
	L23010IR-M5.5-53	2.3 mm / F 10	M 5.5 × P 0.35	IR	1/3.5"	5.16 mm	25°	D: 144° H: 104° V: 74°	10.5	-	-25%	2G2P + IR	
	L23010AR-M5.5-53	2.3 mm / F 10	M 5.5 × P 0.35	IR	1/3.5"	5.16 mm	25°	D: 144° H: 104° V: 74°	10.5	-	-25%	2G2P + IR	
	L23026IR-M5.5-53	2.3 mm / F 2.6	M 5.5 × P 0.35	IR	1/3.5"	5.16 mm	25°	D: 144° H: 104° V: 74°	10.5	-	-25%	2G2P + IR	
	L23026AR-M5.5-53	2.3 mm / F 2.6	M 5.5 × P 0.35	IR	1/3.5"	5.16 mm	25°	D: 144° H: 104° V: 74°	10.5	-	-25%	2G2P + IR	
	L23026AR-M7-53	2.3 mm / F 2.6	M 7 × P 0.5	AR	1/3.5"	5.16 mm	25°	D: 144° H: 104° V: 74°	10.5	-	-25%	2G2P + IR	
	L23026IR-M7-53	2.3 mm / F 2.6	M 7 × P 0.5	IR	1/3.5"	5.16 mm	25°	D: 144° H: 104° V: 74°	10.5	-	-25%	2G2P + IR	
	L23040IR-M5.5-53	2.3 mm / F 4.0	M 5.5 × P 0.35	IR	1/3.5"	5.16 mm	25°	D: 144° H: 104° V: 74°	10.5	-	-25%	2G2P + IR	
	L23050IR-M5.5-53	2.3 mm / F 5.0	M 5.5 × P 0.35	IR	1/3.5"	5.16 mm	25°	D: 144° H: 104° V: 74°	10.5	-	-25%	2G2P + IR	

Image	Model	EFL (mm) Aperture F No.	Mount Thread	Filter	Sensor	Image Circle (mm)	Chief Ray Angle	Field Angle (D x H x V)	Total Track (mm)	Diameter (mm)	TV Distortion	Lens Construction	Note
	L23070IR-M5.5-53	2.3 mm / F 7.0	M 5.5 × P 0.35	IR	1/3.5"	5.16	25°	D: 144° H: 104° V: 74°	10.05	-	-25%	2G2P + IR	
	L23070AR-M5.5-53	2.3 mm / F 7.0	M 5.5 × P 0.35	IR	1/3.5"	5.16	25°	D: 144° H: 104° V: 74°	10.05	-	-25%	2G2P + IR	
	L23070LIR-M5.5-53	2.3 mm / F 7.0	M 5.5 × P 0.35	IR	1/3.5"	5.16	25°	D: 144° H: 104° V: 74°	10.05	-	-25%	2G2P + IR	
	L2125IR-M5.5-52	2.4 mm / F 2.5	M 5.5 × P 0.35	IR	1/3"	5.12	-	D: 158° H: 109° V: 77.6°	-	4.9 (D)		-	
	L2525AR-M12	2.5 mm / F 2.5	M 12 × P 0.5	IR	1/3"	6.2	-	D: 150°	24.24	-		-	
	L2828IR-M12	2.8 mm / F 2.8	M 12 × P 0.5	IR	1/3"	6.2	-	D: 145°	15.8	-		2G2P + IR	
	L3620ARS-C8M9	3.6 mm / F 2.0	M 9 × P 0.5	IR	1/3"	6	-	D: 92° H: 73° V: 54°	14.33	-			
	L3620IRS-C12M9	3.6 mm / F 2.0	M 9 × P 0.5	IR	1/3"	6	-	D: 92° H: 73° V: 54°	14.33	-			
	L4012IR-M12	4.25 mm / F 1.5	M 12 × P 0.5	IR	-	6	-	D: 80° H: 64.2° V: 48.3°	34.45	-	<- 8.3%	9 Components 9 Elements	