



Unit: mm

Specification

Model	3M31828IR-M12
Sensing area	1/3" & 1/2.7"
Focal length	3.18±5%
Back focal length	3.8±0.2% mm (in air)
Flange back length	2.85±0.2% mm
F/NO	2.8±5%
Iris	Fixed
Field of view(D/H/V)	94° / 84° / 54° for AR0230 sensor 86° / 74° / 60° for OV4689 sensor
Resolution	3MP
Distortion	<0.95%
Lens construction	2G 2P IR650nm
Thread sized	M12 x P0.35-6g
M.O.D	0.1m