



UNIT:±0.5mm

Feature

- Miniature size
- High sensitivity!
- High performance.

Specification

Model	MD-V22605L-74
Max. frame rate	1200x1080@ 30fps MJPG
Pixel size	1.4 μm x 1.4 μm
Image sensor	1/8"(D2.26mm) Digital CMOS Camera Module
Image area	1.68x1.51mm
Scan mode	progressive
Sensitivity	553 mV/(Lux-sec)
Dynamic range	73.3 dB @ 15.5x gain
UVC format	MJPEG
Storage temperature	-30 to 60 Degree C
Working temperature	-10 to 45 Degree C
Interface	USB 2.0 (Compliant with USB Video Class 1.1 standard)
Built-in Lens	1.498mm/F5.0
View angle	H= 58° 34'; V= 53° 30'; D= 74° 3'
LED	white LED x 6 (with dimmer control)
Operating system	Windows XP, windows Vista, window 7, windows 8, Windows 10, Mac OS, Linux and Android in OS
Power source	DC 5V (USB)
Power current	160mA
Dimension(mm)	∅5.4

