

**Specification**

Model	MO-P220
Video system	NTSC / PAL
Number of effective pixels	648 x 488 (NTSC / PAL)
Image sensor	1/4" CCIQ Color Camera
Resolution(TV Lines)	400 TV Lines
S/N Ratio	more than 50dB
Minimum illumination	0.1 LUX / F1.2
Frame Rate	60fields/sec(NTSC); 50fields/sec(PAL)
Horizontal sync frequency	NTSC -15.734kHz , PAL- 15.625kHz
Vertical sync frequency	NTSC - 60Hz , PAL - 50Hz
Camera consumption	0.45
Video output	1Vp-p , 75ohm composite
Storage temperature	-30 to 60 Degree C
Working temperature	-10 to 45 Degree C
Built-in Lens	3.9mm F3.9 Pin hole lens
Power source	DC 5~12 V(Standard)
Power current	60 mA

Covert earphone camera for surveillance application.



MO-P220

**Specification**

Model	MJ-P260
Video system	NTSC / PAL
Number of effective pixels	510 x 492 (NTSC) , 628 x 582(PAL)
Image sensor	1/3" CCIQ Color Camera
Resolution(TV Lines)	380 TV Lines
S/N Ratio	more than 48dB
Minimum illumination	0.2 LUX / F1.2
Electronic shutter	1/50-1/12,5000 Sec
Horizontal sync frequency	NTSC(EIA) -15.734kHz , PAL(CCIR) - 15.625kHz
Vertical sync frequency	NTSC(EIA) - 60Hz , PAL(CCIR) - 50Hz
Camera consumption	0.45
Video output	1Vp-p , 75ohm composite
Storage temperature	-30 to 60 Degree C
Working temperature	-10 to 45 Degree C
Built-in Lens	3.9mm F3.9 Pin hole lens
Power source	DC 5~12 V(Standard)
Power current	60 mA



MJ-P260



AF-225  
cable accessory-order in advance

**Connector information**

MODEL	CONNECT	PITCHER	NOTE :
<b>MQ-</b>			<b>G</b> : GND <b>A</b> : AUDIO <b>P</b> : DC POWER <b>V</b> : VIDEO
<b>JQ-</b>			
<b>MJ-</b>		 Ø2.5mm	
<b>MQ-</b>		 Waterproof	

Compatitable with DVR as below:



MP-455E



MP-300E