

Feature:

- Double optical zoom technology, 4K resolution.
- Nondestructive presentation of tissue images at double magnification, the doctor can see the surgical site more closely and clearly.
- Easy to operate and adjust, once focus, the focus is not affected by zoom, the image continues to be clear



Specification

| | | |
|-----------------------|--|--------|
| Model | 8M1432IRB | |
| Focal Length | 14~32mm | |
| Image Format | 1/3" | |
| Mount | CS/C | |
| F No. | F/4 | |
| Pixel | 4K (3840x2160) | |
| Focusing range | 0.1m~∞ | |
| Field Angle (H x V) | D: 25°-11° ,H: 19.6°-8.8, V: 14.6°-6.6° (1:3") | |
| TTL | 58.3mm | |
| Lens construction | 11 elements in 9 groups | |
| Distortion | <2% | |
| Working Wavelength | 400-700nm | |
| Relative Illumination | >0.9 | |
| B.F.L. | 15mm | |
| Operation | Focus | Manual |
| | Zoom | Manual |
| | Iris | Fixed |
| Dimension | Φ49 x 58(L) mm | |
| Gross weight | 140g | |