



B3526




B3526G

3.6 mm / F 2.0 (M 12 x P 0.5)




B3526-4F

4.3 mm / F 2.5 (M 12 x P 0.5)



B3526-2GS

2.28 mm / F 2.0 (M 7 x P 0.5)



Feature

- CCIQ II ► Challenge CCD Image Quality
- Hi Resolution up to 400 TV Lines.
- Compact size
- Ultra-lightweight!
- Backlight compensation
- High Quality Picture
- High Performance
- Outstanding Quality!
- Day & Night Lens

Specification (Camera)

Model No.	B3526G	B3526-4F
Video System	NTSC / PAL	
Effective pixels	648 x 488	
Image Sensor	1/4" CCIQ II Color Camera	
Resolution (TV Lines)	400 TV Lines	
S/N Ratio	More than 50dB	
Minimum Illumination	0.1 Lux / F 1.2	
Electronic Shutter	60 fps.	
Horizontal Sync Frequency	15.734 kHz (NTSC / EIA) 15.625 kHz (PAL / CCIR)	
Vertical Sync Frequency	60 Hz (NTSC / EIA) 50 Hz (PAL / CCIR)	
Camera Consumption	0.45	
Video Output	1 Vp-p , 75 ohm Composite	
Storage Temperature	-30 to 60 Degree C	
Working Temperature	-10 to 45 Degree C	
Lens	3.6 mm / F 2.0	4.3 mm / F 2.5
Power Source	DC 5~12 V (Standard)	
Power Current	100 mA	80 mA
Dimension (mm)	22 x 26 (mm)	

MO-B3526YA-3C

SERIES	CONNECTOR	CAMERA BODY	DISPLAY	Day & Night	MICROPHONE	LENS
M Basic	O Mini 4 Pin	F Front View B Board Type	3526 Board Type Color G-Type 3526G Color	Y Adopt N/A None	A External N/A None	2GS Board Type 2.1 mm / F 2.5 G-Type 3C 3.7 mm / F 2.0 Cone 3F 3.7 mm / F 2.0 Flat 3T 3.1 mm / F 3.4 Flat 4C 4.3 mm / F 2.0 Cone 4F 4.3 mm / F 2.0 Flat 4T 3.9 mm / F 3.9 Flat G-Type N/A 3.6 mm / F 2.0 G-Type * 2GS Super Wide-Angle 158°

Other Information

MO-N3531
1/4" Color Hidden Camera

