



Unit : ± 0.5 mm

### Specification

Model	AHD-S41488	CVI-S41488	TVI-S41488	N/A
Video Format	AHD	CVI	TVI	PVI
Pixel Size (µm)	2.8 x 2.8			
Effective Image Area (mm)	3.6064 x 2.0384			
Number Of Effective Pixels	1280 (H) x 720 (V)			
Image Sensor	1/4" Color CCIQ Camera			
S/N Ratio	43.3 [dB]			
Dynamic Range	66.9 [dB]			
Sensitivity	22.5K [e/Lux.sec]			
Storage Temperature	-30 to 60 Degree C			
Working Temperature	-10 to 45 Degree C			
Power Source	DC 5~12 V			
Power Current	40 mA (DC 12V) / 100 mA (DC 5V)			
Dimension (mm)	8.6 x 8.6			

## AHD-S41488A-2E

SERIES	CAMERA TYPE	MICROPHONE	LENS			
			Code	Specification	Thread	View Angle
AHD AHD CVI CVI TVI TVI	S41488 Forming Type	A Microphone	2E	2.3 mm / F 2.6	M 7 × P 0.5	104°
		N/A None	2ES	2.3 mm / F 2.6	M 5.5 × P 0.35	104°
			3K	2.8 mm / F 3.9	M 5.5 × P 0.35	79°
			2V	2.83 mm / F3.9	M 7 × P 0.5	79°
			3T	3.4 mm / F 3.4	M 7 × P 0.5	67°
			3M	3.4 mm / F 2.8	M 6 × P 0.35	62°
			3X6	3.4 mm / F 6.0	M 6 × P 0.35	62°
			4T	3.9 mm / F 3.9	M 7 × P 0.5	55°
			4H	4.5 mm / F 2.8	M 7 × P 0.5	49°

\* 3X6 With High DOF

### Feature

- Compact Size.
- Hi Resolution 720p.
- High Performance.
- Outstanding Quality!

